




FIG. 1



Without pressure of slide:	With pressure of slide:	Durchmesser
		2 min: 1.2 cm 10 min: 1.2 cm
		2 min: 4.5 cm 10 min: Flowed out the cover glass
		2 min: 2.1 cm 10 min: 2.3 cm

FIG. 2




FIG. 3

4/10




FIG. 4

5/10




FIG. 5




FIG. 6





FIG. 7



Aerosil 200 3 % Aerosil 200 4 % Aerosil 200 3 % Aerosil 200 3 % Aerosil 200 3 % Aerosil 200 3 % Aerosil 200 3 % Aerosil 200 3 %
Referenz Syloblanc 0.5 % Syloblanc 1.0 % Syloblanc 1.5 % Syloblanc 2.0 % Syloblanc 3.0 % Syloblanc 5.0 %

FIG. 8




FIG. 9




FIG. 10A




FIG. 10B




FIG. 10C




FIG. 10D




FIG. 10E