



(51) International Patent Classification:

G01N 29/24 (2006.01) G01N 29/265 (2006.01)
G01N 29/04 (2006.01) G01N 29/28 (2006.01)
B05B 7/24 (2006.01)

(21) International Application Number:

PCT/US2023/023929

(22) International Filing Date:

31 May 2023 (31.05.2023)

(25) Filing Language:

English

(26) Publication Language:

English

(30) Priority Data:

63/347,760 01 June 2022 (01.06.2022) US
18/324,818 26 May 2023 (26.05.2023) US

(72) Inventors; and

(71) Applicants: **BRIGGS, IV, Fred Melville** [US/US]; c/o Applied Impact Robotics, Inc., 45449 Severn Way, Suite 165, Sterling, Virginia 20166 (US). **WERNICK, Brandon Pollett** [US/US]; c/o Applied Impact Robotics, Inc., 45449 Severn Way, Suite 165, Sterling, Virginia 20166 (US). **LLOYD, Nathan Alexander** [US/US]; c/o Applied Im-

pact Robotics, Inc., 45449 Severn Way, Suite 165, Sterling, Virginia 20166 (US). **SAMOTSHOZO, Ernest Wardell** [US/US]; c/o Applied Impact Robotics, Inc., 45449 Severn Way, Suite 165, Sterling, Virginia 20166 (US).

(74) Agent: **HANSEN, Robert et al.**; The Marbury Law Group, PLLC, 11800 Sunrise Valley Dr.; 15th Floor, Reston, Virginia 20191 (US).

(81) Designated States (unless otherwise indicated, for every kind of national protection available): AE, AG, AL, AM, AO, AT, AU, AZ, BA, BB, BG, BH, BN, BR, BW, BY, BZ, CA, CH, CL, CN, CO, CR, CU, CV, CZ, DE, DJ, DK, DM, DO, DZ, EC, EE, EG, ES, FI, GB, GD, GE, GH, GM, GT, HN, HR, HU, ID, IL, IN, IQ, IR, IS, IT, JM, JO, JP, KE, KG, KH, KN, KP, KR, KW, KZ, LA, LC, LK, LR, LS, LU, LY, MA, MD, MG, MK, MN, MU, MW, MX, MY, MZ, NA, NG, NI, NO, NZ, OM, PA, PE, PG, PH, PL, PT, QA, RO, RS, RU, RW, SA, SC, SD, SE, SG, SK, SL, ST, SV, SY, TH, TJ, TM, TN, TR, TT, TZ, UA, UG, US, UZ, VC, VN, WS, ZA, ZM, ZW.

(84) Designated States (unless otherwise indicated, for every kind of regional protection available): ARIPO (BW, CV,

(54) Title: UT SENSOR INTERFACE FOR SCANNING IN COMPLEX ENVIRONMENTS




FIG. 3

(57) Abstract: A UT scanner interface may include a main body that includes an inner chamber including a UT scanner facing toward an opening on a bottom side, a couplant injection port, and a fluid evacuation port. During operations, a couplant is injected into the inner chamber via the couplant injection port while couplant and any contaminants may be removed from the inner chamber via the fluid evacuation port.

[Continued on next page]

GH, GM, KE, LR, LS, MW, MZ, NA, RW, SC, SD, SL, ST, SZ, TZ, UG, ZM, ZW), Eurasian (AM, AZ, BY, KG, KZ, RU, TJ, TM), European (AL, AT, BE, BG, CH, CY, CZ, DE, DK, EE, ES, FI, FR, GB, GR, HR, HU, IE, IS, IT, LT, LU, LV, MC, ME, MK, MT, NL, NO, PL, PT, RO, RS, SE, SI, SK, SM, TR), OAPI (BF, BJ, CF, CG, CI, CM, GA, GN, GQ, GW, KM, ML, MR, NE, SN, TD, TG).

Published:

— with international search report (Art. 21(3))